

Cleanroom Wipers

Dry | Pre-Wetted | Sterile | Non Sterile

VERTEX® | VECTRA® SEALED-BORDER | SEALED-EDGE | CUT-EDGE | NONWOVEN | SPECIALTY



texwipe.com

Table of Contents

Vertex® Wipers

Vectra® Sealed-Border Wipers

Sealed-Edge Wipers

Cut-Edge Wipers

Nonwoven Wipers

Specialty Wipers

About Texwipe

Texwipe's commitment to innovation, leadership and quality in cleanroom consumable products spans more than fifty years. We invest in technology to respond to our customers' evolving needs in contamination control.

Texwipe's Core Values are:

- Innovation Texwipe pioneers the latest technologies to provide innovation in contamination control products and processes.
- Quality Texwipe product quality is maintained by the most advanced testing and quality control standards in the industry.
- Technology Leadership Texwipe leads our industry in testing metrology, methods and processes to reduce contamination.

Throughout Texwipe's global operations, we support our customers with products designed to exceed the requirements for cleanroom consumable products. Our highly professional team will help you select and develop products for any critical environment application.

Texwipe: The Leader in Critical Cleaning Products

Product Development

Texwipe is committed to supplying the highest quality, most consistent cleanroom consumable products. We invest in technology, innovation and quality to create and maintain state-of-the-art systems. www.texwipe.com.

Metrology

Many of the standard test methods used in the cleanroom wiper industry were developed by Texwipe. All sterile products are tested for endotoxins.

Manufacturing

Texwipe developed key manufacturing breakthroughs in cleanroom wipers including Vertex® and Vectra® Sealed-Edge.

Technical Support

Technical and practical support is supplied directly to customers to ensure effective cleaning protocols.

Product and Customer Support

Texwipe is the technical and market leader in cleanroom wipers. We provide innovative materials and services for cleaning critical environments in the electronics, pharmaceutical and medical device industries.

To support your needs, we provide:

- On-site Facility Audits
- Technical Training
- Technical Articles and Data Sheets
- Product Line Brochures and Guides
- Sample Binders
- Test Methods
- Website and Web-Store www.texwipe.com







INDUSTRIES				
Aerospace	Animal Laboratory			
Biologics	Cleanroom Design/Build			
Cleanroom Environment	Compounding Pharmacies			
Data Storage	Facilities Maintenance			
Industrial	Laboratory			
Medical Device	Microelectronics			
Pharmaceutical	Printing/Graphics			
Semiconductor	USP <797> / USP <800>			

Vertex® Wiper Series

- 100% polyester material with a sealed edge/laser edge processed on Texwipe's fully automated manufacturing system.
- Vertex® advances wiper manufacturing technology, bringing it to the highest level in the industry.
- Low levels of ions, NVRs (non volatile residues), particles and fibers for use in critical cleaning applications and environments such as wiping and cleaning surfaces, equipment and parts
- Vertex® wipers are designed for high sorption capacity ideal for spill control, cleaning and solution application.
- Tested for cytotoxicity and bacterial endotoxins for an extra level of contamination control assurance with consistent, optimized cleaning efficiency with repeatable wetness and VOC levels.
- Meets USP <797> and USP <800> requirements and are autoclave safe (dry wipers only).
- Individually lot coded for ease of traceability and quality control

Pre-Wetted

- Easy-to-use, recloseable slider bags reducing solution evaporation.
- Pre-wetted with 0.2 μm filtered 70% IPA / 30% DIW or 70% Denatured Ethanol / 30% DIW.
- Available dry (Vertex[®]), pre-wetted (Vertex[®] pre-wetted) and sterile.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
Vertex®	9" x 9"	TX29 TX49	TX49P	TX3049	TX3049P
	11" x 11"	_	_	TX3221	_
	12" x 12"	TX42	TX42P	TX3042	TX3042P TX3044P

Vertex®



Vertex® Microdenier Wipers

- 100% polyester, nylon-free, material with a sealed edge processed on Texwipe's fully automated manufacturing system. Vertex® advances wiper manufacturing technology, bringing it to the highest level in the industry.
- Offers increased lifting and capturing of particles as small as microbes.
- Quick wicking performance makes them ideal for streak-free cleaning and spill control.
- Unique microdenier construction allows the removal of oils and fingerprints.
- Ideal for surfaces susceptible to scratching and are nylon-free and compatible for applying Quaternary Ammonium Compounds (Quats) and other disinfectants and cleaners.
- Tested for cytotoxicity and bacterial endotoxins for an extra level of contamination control assurance and are manufactured to provide low levels of particles and extractables, creating a wiper suitable for critical cleaning and wiping.
- Meets USP <797> and USP <800> requirements and are autoclave safe.
- Individually lot coded for ease of traceability and quality control.
- Available dry (Vertex[®] Microdenier) and sterile.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
Vertex® Microdenier	9" x 9"	TX59	_	TX3059	_

IND		TRIES	
	Aerospace	Animal Laboratory	
	Biologics	Cleanroom Design/Build	
	Cleanroom Environment	Compounding Pharmacies	
	Data Storage	Facilities Maintenance	
	Industrial	Laboratory	
	Medical Device	Microelectronics	
	Pharmaceutical	Printing/Graphics	
	Semiconductor	USP <797> / USP <800>	



INDUSTRIES		
Aerospace	Animal Laboratory	
Biologics	Cleanroom Design/Build	
Cleanroom Environment	Compounding Pharmacies	
Data Storage	Facilities Maintenance	
Industrial	Laboratory	
Medical Device	Microelectronics	
Pharmaceutical	Printing/Graphics	
Semiconductor	USP <797> / USP <800>	

Vectra® Alpha® 10

- 100% polyester with a sealed-border. Processed on Texwipe's automated cleaning system. Vectra® advances the cleaning process and brings this technology to a higher level of wiper manufacturing.
- Vectra sealed-border technology provides low levels of ions, NVRs (non volatile residues), particles and fibers for use in critical cleaning applications and environments.
- Use on abrasive surfaces will not easily snag or abrade releasing particles and fibers into the process or environment.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Meets USP <797> and USP <800> requirements.
- Autoclave safe (dry wipers only).
- Individually lot coded for ease of traceability and quality control

Pre-Wetted

- AlphaSat® with Vectra® Alpha® 10 wipers are pre-wetted with 0.2 μm filtered 70% IPA / 30% DIW, 10% IPA / 90% DIW or 6% IPA / 94% DIW for ease of use and provide consistent, optimized cleaning efficiency with repeatable wetness and VOC levels.
- Easy-to-use, recloseable slider and peel-and-reseal bags reduces solution evaporation that preserves consistent wiper wetness level.

	Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
	Vectra®	9" x 9"	TX1010	TX8410	_	TX3285
	Alpha® 10	12" x 12"	TX1012	TX8415	TX3212	TX3280

Vectra® Sealed-Border



Vectra® Alpha 10 LT

- Low titanium dioxide (TiO2) 100% polyester with a sealed-border, processed on Texwipe's automated cleaning system. Vectra® advances the cleaning process and brings this technology to a higher level of wiper manufacturing. Designed with a low level of titanium dioxide (TiO2), safe for processes that are affected by the presence of TiO2. The presence of TiO2 may leave an additional residue.
- Vectra® sealed-border technology provides low levels of ions, NVRs (non-volatile residues), particles and fibers for use in critical cleaning applications and environments.
- Use on abrasive surfaces will not easily snag or abrade releasing particles and fibers into the process or environment.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Autoclave safe (dry wipers only).
- Individually lot coded for ease of traceability and quality control.

Pre-Wetted

- Vectra® QuanSat™ LT is pre-wetted with 0.2 µm filtered 6% IPA / 94% DIW for ease of use.
- Easy-to-use recloseable slider bags reduces solution evaporation that preserves consistent wiper wetness level.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
Vectra® Alpha® 10 LT	9" x 9"	TX8659	TX8691	_	_

For more detailed information contact your Texwipe representative at 1-800-TEXWIPE or visit us online at www.texwipe.com

INDUS	TRIES
Aerospace	Animal Laboratory
Biologics	Cleanroom Design/Build
Cleanroom Environment	Compounding Pharmacies
Data Storage	Facilities Maintenance
Industrial	Laboratory
Medical Device	Microelectronics
Pharmaceutical	Printing/Graphics
Semiconductor	USP <797> / USP <800>

Vectra® AlphaSorb® 10

- 100% two-ply polyester material with a sealed-border, processed on Texwipe's automated cleaning system. Vectra® advances the cleaning process and brings this technology to a higher level of wiper manufacturing.
- Constructed from a double layer of polyester material creating a high sorption wiper ideal for spill control, cleaning, and solution application.
- Vectra® border seal technology provides low levels of ions, NVRs (non-volatile residues), particles and fibers for use in critical applications and environments.
- Use on abrasive surfaces will not easily snag or abrade releasing particles and fibers into the process or environment.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Meets USP <797> and USP <800> wiper requirements.
- Autoclave safe (dry wipers only).
- Individually lot coded for ease of traceability and quality control.

Pre-Wetted

- AlphaSat[®] with Vectra[®] AlphaSorb[®] 10 wipers are pre-wetted with 0.2 μm filtered 10% IPA / 90% DIW for ease of use and provide a consistent, optimized cleaning efficiency with repeatable wetness and VOC level.
- Easy-to-use, recloseable slider bags reducing solution evaporation that preserves the consistent wiper wetness level.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
Vectra® AlphaSorb®	9" x 9"	TX1050	TX1057	_	_
10	12" x 12"	TX1052	_	TX3215	_

Vectra® Sealed-Border



Vectra® Honeycomb® 10

- 100% polyester with a sealed-border processed on Texwipe's automated cleaning system. Vectra® advances the cleaning process and brings this technology to a higher level of wiper manufacturing.
- Designed to combine the benefits of two wipers in one. One side contains honeycomb pockets for capturing and retaining particles including debris. The other side is smooth. Together, they form a high sorption wiper ideal for spill control, cleaning, and solution application.
- Vectra sealed-border technology provides low levels of ions, NVRs (non volatile residues), particles and fibers for use in critical cleaning applications and environments.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Meets USP <797> and USP <800> wiper requirements.
- Autoclave safe.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
Vectra® Honeycomb® 10	9" x 9"	TX1060	_	_	_

INDUS	TRIES			
Aerospace	Animal Laboratory			
Biologics	Cleanroom Design/Build			
Cleanroom Environment	Compounding Pharmacies			
Data Storage	Facilities Maintenance			
Industrial	Laboratory			
Medical Device	Microelectronics			
Pharmaceutical	Printing/Graphics			
Semiconductor	USP <797> / USP <800>			

Vectra® Sealed-Border



	INDUSTRIES		
	Aerospace	Animal Laboratory	
	Biologics	Cleanroom Design/Build	
	Cleanroom Environment	Compounding Pharmacies	
	Data Storage	Facilities Maintenance	
	Industrial	Laboratory	
	Medical Device	Microelectronics	
	Pharmaceutical	Printing/Graphics	
	Semiconductor	USP <797> / USP <800>	

Vectra® QuanTex™


- 100% polyester with a sealed-border processed on Texwipe's automated cleaning system. Vectra® advances the cleaning process and brings this technology to a higher level of wiper manufacturing.
- Each lot of QuanTex[™] polyester wipers are tested for cytotoxicity by the Agar Overlay method and for Bacterial Endotoxins by LAL (Limulus Amebocyte Lysate) test for an extra level of contamination control assurance. Reports available upon request (TX1086 not applicable).
- Vectra® sealed-border technology provides low levels of ions, NVRs (non-volatile residues), particles and fibers for use in critical cleaning applications and environments – ideal for spill control, cleaning, and solution application.
- Meets USP <797> and USP <800> wiper requirements.
- Autoclave safe (dry wipers only).
- Individually lot coded for ease of traceability and quality control.

Pre-Wetted

- Vectra® QuanSat[™] products are pre-wetted with 0.2 µm filtered 100% IPA, 70% IPA / 30% DIW or 6% IPA / 94% DIW for ease of use and provide a consistent, optimized cleaning efficiency with repeatable wetness and VOC levels.
- Easy-to-use, recloseable slider bags reduce solution evaporation that preserves the consistent wiper wetness level.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
Vectra® QuanTex™	9" x 9"	TX1080	TX1082 TX1084 TX1086	_	_

Vectra® Sealed-Border



Vectra® Quantum® 100

- 100% polyester with a sealed-border processed on Texwipe's automated cleaning system.
- Vectra® advances the cleaning process and brings this technology to a higher level of wiper manufacturing. Vectra® sealed-border technology provides low levels of ions, NVRs (non-volatile residues), particles and fibers for use in critical cleaning applications and environments.
- Ideal for spill control, cleaning, and solution application.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Meets USP <797> and USP <800> wiper requirements.
- Autoclave safe.
- Individually lot coded for ease of traceability and quality control.

Co	llection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
Vecti Quar	ra® itum®	9" x 9"	TX1029	_	_	_

INDUS	INDUSTRIES			
Aerospace	Animal Laboratory			
Biologics	Cleanroom Design/Build			
Cleanroom Environment	Compounding Pharmacies			
Data Storage	Facilities Maintenance			
Industrial	Laboratory			
Medical Device	Microelectronics			
Pharmaceutical	Printing/Graphics			
Semiconductor	USP <797> / USP <800>			

Sealed-Border



101213101012 CC 22					
INDUS	TRIES				
Aerospace	Animal Laboratory				
Biologics	Cleanroom Design/Build				
Cleanroom Environment	Compounding Pharmacies				
Data Storage	Facilities Maintenance				
Industrial	Laboratory				
Medical Device	Microelectronics				
Pharmaceutical	Printing/Graphics				
Semiconductor	USP <797> / USP <800>				

TexTra[™] 10

- TexTra[™] 10 is made from 100% polyester with a sealed border, cleanroom laundered, providing low levels of ions and NVRs (non-volatile residues) particles. Constructed from a single layer of polyester, equivalent to a two-ply absorbent capacity, creating a high absorbency wiper ideal for spill control, cleaning, and solution application.
- Use on abrasive surfaces will not easily snag or abrade releasing particles and fibers into the process or environment.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Meets USP <797> and USP <800> wiper requirements.
- Autoclave safe.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
TexTra™ 10	9" x 9"	_	_	TX3224	_
	12" x 12"	TX2452	_	TX3225	_

Sealed-Border



TexTube® Wipers

- Two-ply 100% polyester with two sealed-border ends and rounded sides and is cleanroom laundered. Constructed from a double layer of polyester fabric creating a wiper with high absorption capacity, making it ideal for spill control, cleaning, and solution application.
- Manufactured to provide low levels of particles and extractables creating a wiper suitable for general cleaning and wiping.
- Use on abrasive surfaces will not easily snag or abrade releasing particles and fibers into the process or environment.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Meets USP <797> and USP <800> wiper requirements.
- Autoclave safe.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
TexTube®	9" x 9"	TX1070	_	_	_

INDUSTRIES				
Aerospace	Animal Laboratory			
Biologics	Cleanroom Design/Build			
Cleanroom Environment	Compounding Pharmacies			
Data Storage	Facilities Maintenance			
Industrial	Laboratory			
Medical Device	Microelectronics			
Pharmaceutical	Printing/Graphics			
Semiconductor	USP <797> / USP <800>			



Sealed-Edge



INDUSTRIES			
Aerospace	Animal Laboratory		
Biologics	Cleanroom Design/Build		
Cleanroom Environment	Compounding Pharmacies		
Data Storage	Facilities Maintenance		
Industrial	Laboratory		
Medical Device	Microelectronics		
Pharmaceutical	Printing/Graphics		
Semiconductor	USP <797> / USP <800>		

TexVantage[™] Polyester

- 100% polyester with a sealed edge, creating a wiper ideal for spill control, cleaning and solution application.
- Use on abrasive surfaces will not easily snag or abrade releasing particles and fibers into the process or environment.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Meets USP <797> and USP <800> wiper requirements.
- Autoclave safe.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
TexVantage [™]	4" x 4"	TX8944	_	_	_
Polyester	9" x 9"	TX8949	_	_	_
	12" x 12"	TX8942	_	_	_

Sealed-Edge



ThermaSeal[™] 60

- 100% polyester with a sealed edge and cleanroom laundered, providing low levels of ions and NVRs (non-volatile residues) particles, creating a wiper ideal for spill control, cleaning, and solution application.
- Use on abrasive surfaces will not easily snag or abrade releasing particles and fibers into the process or environment.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Meets USP <797> and USP <800> wiper requirements.
- Autoclave safe.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
ThermaSeal™	4" x 4"	TX2064	_	_	_
60	9" x 9"	TX2069	_	_	_

INDUSTRIES					
Aerospace	Animal Laboratory				
Biologics	Cleanroom Design/Build				
Cleanroom Environment	Compounding Pharmacies				
Data Storage	Facilities Maintenance				
Industrial	Laboratory				
Medical Device	Microelectronics				
Pharmaceutical	Printing/Graphics				
Semiconductor	USP <797> / USP <800>				



Sealed-Edge



INDUSTRIES Aerospace Animal Laboratory Biologics Cleanroom Design/Build Compounding Pharmacies Cleanroom Environment Data Storage Facilities Maintenance Industrial Laboratory Medical Device Microelectronics Pharmaceutical Printing/Graphics USP <797> / USP <800> Semiconductor

Alpha® 1 Microfiber

- 80% polyester / 20% nylon with a sealed edge, ideal for surfaces susceptible to scratching.
- Quick wicking performance creates a wiper ideal for spill control, streak-free cleaning and solution application with increased lifting and capturing of particles as small as microbes.
- Unique microfiber construction allows the removal of oils and fingerprints.
- Provides low levels of particles and extractables creating a wiper suitable for critical cleaning and wiping.
- Meets USP <797> and USP <800> wiper requirements.
- Autoclave safe.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
Alpha®1	4" x 4"	TX1204	_	_	_
Microfiber	6" x 6"	TX1206	_	_	_
	9" x 9"	TX1209	_	STX1209	_
	12" x 12"	TX1212	_	STX1212	_



Cut-Edge



INDUSTRIES Animal Laboratory Aerospace Biologics Cleanroom Design/Build Compounding Pharmacies Cleanroom Environment Facilities Maintenance Data Storage Industrial Laboratory Microelectronics Medical Device Printing/Graphics Pharmaceutical USP <797> / USP <800> Semiconductor

AlphaLite[®]

- 100% polyester with a cut edge, cleanroom laundered, providing low levels of ions and NVRs (non-volatile residues) particles, creating a wiper ideal for spill control, cleaning and solution application.
- Use on abrasive surfaces will not easily snag or abrade releasing particles and fibers into the process or environment.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Meets USP <797> and USP <800> wiper requirements.
- Autoclave safe.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
AlphaLite®	9" x 9"	TX1008 TX1008B	_	_	_

Cut-Edge



AlphaSorb® HC

- 100% two-ply polyester with a cut edge, cleanroom laundered, providing low levels of ions and NVRs (non-volatile residues) particles.
- Constructed from a double layer of polyester material creating a high absorbency wiper ideal for spill control, cleaning, and solution application.
- Use on abrasive surfaces will not easily snag or abrade releasing particles and fibers into the process or environment.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Autoclave safe (dry wipers only).
- Individually lot coded for ease of traceability and quality control.

Pre-Wetted

AlphaSat® with AlphaSorb®HC is pre-wetted with 70% IPA / 30% DIW for ease of use.

	Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
	AlphaSorb® HC	9" x 9"	TX2409	_	_	_
		12" x 12"	TX2412	_	_	TX3252
		18" x 18"	TX2418	_	_	_

INDUSTRIES				
Aerospace	Animal Laboratory			
Biologics	Cleanroom Design/Build			
Cleanroom Environment	Compounding Pharmacies			
Data Storage	Facilities Maintenance			
Industrial	Laboratory			
Medical Device	Microelectronics			
Pharmaceutical	Printing/Graphics			
Semiconductor	USP <797> / USP <800>			

Cut-Edge



INDUSTRIES				
Aerospace	Animal Laboratory			
Biologics	Cleanroom Design/Build			
Cleanroom Environment	Compounding Pharmacies			
Data Storage	Facilities Maintenance			
Industrial	Laboratory			
Medical Device	Microelectronics			
Pharmaceutical	Printing/Graphics			
Semiconductor	USP <797> / USP <800>			

AlphaWipe®

- 100% polyester material with a cut edge, cleanroom laundered and packaged providing ultra low levels of ions and non volatile residues. Constructed from 100% polyester creating a high absorbency wiper ideal for spill control, cleaning, and solution application.
- Use on abrasive surfaces will not easily snag or abrade releasing particles and fibers into the process or environment.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Meets USP <797> and USP <800> wiper requirements.
- Autoclave safe (dry wipe).
- Individually lot coded for ease of traceability and quality control.

Pre-Wetted

- AlphaSat® products are pre-wetted with 0.2 µm filtered 70% IPA / 30% DIW or 6% IPA / 94% DIW for ease of use, providing a consistent, optimized cleaning efficiency with repeatable wetness and VOC levels.
- Packaged in easy-to-use, recloseable slider bags, reduces solution evaporation that preserves the consistent wiper wetness level.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
AlphaWipe®	4" x 4"	TX1004	TX1034	STX1004	STX1034
	6" x 6"	_	TX1036	_	_
	9" x 9"	TX1009 TX1009B	TX1039	TX3211	_
	9" x 31"	_	TX7031	_	_
	9" x 32"	TX1031	_	_	_
	12" x 12"	TX1013	_	_	_
	24" x 44"	TX1025	_	_	_

Cut-Edge



MiracleWipe®

- 100% nylon material with a cut edge, cleanroom laundered and packaged, providing low levels of ions and NVRs (non volatile residues).
- Constructed from 100% nylon creating a high absorbency wiper ideal for spill control, cleaning, and solution application.
- Unique texture that provides scrubbing surface for cleaning.
- Good chemical resistance for compatibility with a variety of solutions.
- Autoclave safe.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
MiracleWipe®	4" x 4"	TX4004	_	_	_
	9" x 9"	TX4009	_	_	_
	12" x 12"	TX4012	_	_	_

INDUS	INDUSTRIES				
Aerospace	Animal Laboratory				
Biologics	Cleanroom Design/Build				
Cleanroom Environment	Compounding Pharmacies				
Data Storage	Facilities Maintenance				
Industrial	Laboratory				
Medical Device	Microelectronics				
Pharmaceutical	Printing/Graphics				
Semiconductor	USP <797> / USP <800>				



Cut-Edge



INDUS	STRIES	
Aerospace	Animal Laboratory	
Biologics	Cleanroom Design/Build	
Cleanroom Environment	Compounding Pharmacies	
Data Storage	Facilities Maintenance	
Industrial	Laboratory	
Medical Device	Microelectronics	
Pharmaceutical	Printing/Graphics	
Semiconductor	USP <797> / USP <800>	

TexTra®

- 100% polyester with a cut edge, cleanroom laundered, providing low levels of ions and NVRs (non-volatile residues) particles.
- Constructed from a single layer of polyester, equivalent to a two-ply absorbent capacity creating a high absorbency wiper ideal for spill control, cleaning, and solution application.
- Use on abrasive surfaces will not easily snag or abrade releasing particles and fibers into the process or environment.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Meets USP <797> and USP <800> wiper requirements.
- Autoclave safe.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
TexTra®	12" x 12"	TX2424	_	TX3220	_





INDUSTRIES			
Aerospace	Animal Laboratory		
Biologics	Cleanroom Design/Build		
Cleanroom Environment	Compounding Pharmacies		
Data Storage	Facilities Maintenance		
Industrial	Laboratory		
Medical Device	Microelectronics		
Pharmaceutical	Printing/Graphics		
Semiconductor	USP <797> / USP <800>		

Absorbond®

- 100% polyester nonwoven material with a cut edge, cleanroom manufactured to provide low levels of ions and NVRs (non-volatile residues) creating a wiper suitable for critical environments.
- Soft, non-abrasive wiper ideal for use on scratch-sensitive surfaces.
- Excellent chemical resistance for compatibility with a variety of solutions and a high absorbency with isopropyl (IPA) solutions.
- Autoclave safe.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
Absorbond®	4" x 4"	TX404	_	_	_
	9" x 9"	TX409	_	_	_

Nonwoven



BlueWipe®

- 45% polyester / 55% cellulose nonwoven colorfast material with a cut edge, cleanroom manufactured, creating a durable wiper ideal for spill control, cleaning, and solution application.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Packaged in a C-fold design for easy access and removal from the center of the bag.
- Meets USP <797> and USP <800> wiper requirements.
- Autoclave safe.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
BlueWipe®	12" x 12"	TX512	_	_	_

INDUSTRIES				
Aerospace	Animal Laboratory			
Biologics	Cleanroom Design/Build			
Cleanroom Environment	Compounding Pharmacies			
Data Storage	Facilities Maintenance			
Industrial	Laboratory			
Medical Device	Microelectronics			
Pharmaceutical	Printing/Graphics			
Semiconductor	USP <797> / USP <800>			



INDUSTRIES			
Aerospace	Animal Laboratory		
Biologics	Cleanroom Design/Build		
Cleanroom Environment	Compounding Pharmacies		
Data Storage	Facilities Maintenance		
Industrial	Laboratory		
Medical Device	Microelectronics		
Pharmaceutical	Printing/Graphics		
Semiconductor			

ProCell™

- Cleanroom manufactured from 35% polypropylene (outer layers) / 65% cellulose (inner layer) nonwoven material with a cut edge, creating a wiper ideal for spill control, cleaning, and solution
- Suitable for general cleaning and wiping with excellent chemical resistance for compatibility with a variety of solutions.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
ProCell™	9" x 9"	TX699	_	_	_

Nonwoven



TechniCloth®

- 45% polyester / 55% cellulose nonwoven material with a cut edge, cleanroom manufactured, creating a durable wiper ideal for spill control, cleaning, and solution application.
- Provides low levels of particles and extractables creating a wiper suitable for general cleaning and wiping with excellent chemical resistance for compatibility with a variety of solutions.
- Autoclave safe (dry wipers only).
- Meets USP <797> and USP <800> wiper requirements.
- Individually lot coded for ease of traceability and quality control.

Pre-Wetted

- TechniSat® products are pre-wetted with 0.2 µm filtered 70% IPA / 30% DIW, 6% IPA/ 94% DIW or 70% Denatured Ethanol / 30% DIW for ease of use and provide consistent, optimized cleaning efficiency with repeatable wetness and VOC levels.
- Easy-to-use, recloseable slider bags, flip-top canisters, tubs, and peel-and-reseal bags reducing solution evaporation that preserves the consistent wiper wetness level.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
TechniCloth®	4" x 4"	TX604	_	_	_
	6" x 6"	TX606	_	_	_
	6" x 8"	_	TX1045	_	_
	7" x 11"	_	TX1067 TX1068	_	STX1068
	8" x 5"	_	TX1048	_	
	8" x 5.5"	_	_	_	STX1041
	9" x 9"	TX609	_	STX609	_
	9" x 11"	_	TX1041 TX1065 TX8488	_	TX3214 TX3217
	12" x 12"	TX612	_	TX3210	_

INDUSTRIES					
Aerospace	Animal Laboratory				
Biologics	Cleanroom Design/Build				
Cleanroom Environment	Compounding Pharmacies				
Data Storage	Facilities Maintenance				
Industrial	Laboratory				
Medical Device	Microelectronics				
Pharmaceutical	Printing/Graphics				
Semiconductor	USP <797> / USP <800>				



INDUSTRIES				
Aerospace	Animal Laboratory			
Biologics	Cleanroom Design/Build			
Cleanroom Environment	Compounding Pharmacies			
Data Storage	Facilities Maintenance			
Industrial	Laboratory			
Medical Device	Microelectronics			
Pharmaceutical	Printing/Graphics			
Semiconductor	USP <797> / USP <800>			

Cleanroom Wipers | texwipe.com

TechniCloth II®

- Constructed from proprietary coated 45% polyester / 55% cellulose nonwoven material with a cut edge, cleanroom manufactured, creating a durable wiper ideal for spill control, cleaning, and solution application.
- Manufacturing process incorporates a proprietary coating that provides low levels of particles and extractables creating a wiper suitable for general cleaning and wiping.
- Good chemical resistance for compatibility with a variety of solutions.
- Meets USP <797> and USP <800> wiper requirements.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
Technicloth II®	9" x 9"	TX1109	_	_	_
	12" x 12"	TX1112	_	_	_
	18" x 18"	TX1118	_	_	_

Nonwoven



TechniScrub™

- 50% polyester / 50% cellulose nonwoven material with a cut edge, cleanroom manufactured, creating a durable wiper with a textured side for removing deposits and a smooth side for follow-up wiping and cleaning.
- Superior sorption capacity.
- Provides low levels of particles and extractables creating a wiper suitable for general cleaning and wiping with excellent chemical resistance for compatibility with a variety of solutions.
- Autoclave safe.
- Meets USP <797> and USP <800> wiper requirements.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
TechniScrub™	9" x 9"	TX4409	_	_	_
	12" x 12"	TX4412	_	_	_





1 3 3 4 7 47 3 b - 3					
INDUSTRIES					
Aerospace	Animal Laboratory				
Biologics	Cleanroom Design/Build				
Cleanroom Environment	Compounding Pharmacies				
Data Storage	Facilities Maintenance				
Industrial	Laboratory				
Medical Device	Microelectronics				
Pharmaceutical	Printing/Graphics				
Semiconductor	USP <797> / USP <800>				



INDUSTRIES			
Aerospace	Animal Laboratory		
Biologics	Cleanroom Design/Build		
Cleanroom Environment	Compounding Pharmacies		
Data Storage	Facilities Maintenance		
Industrial	Laboratory		
Medical Device	Microelectronics		
Pharmaceutical	Printing/Graphics		
Semiconductor	USP <797> / USP <800>		
	Aerospace Biologics Cleanroom Environment Data Storage Industrial Medical Device Pharmaceutical		

TexVantage[™] Nonwoven

- 40% polyester / 60% cellulose nonwoven material with a cut edge, cleanroom manufactured, creating a durable wiper ideal for spill control, cleaning, and solution application.
- Manufactured to provide a wiper suitable for general cleaning and wiping.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Meets USP <797> and USP <800> wiper requirements.
- Autoclave safe.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
TexVantage [™]	9" x 9"	TX8939	_	_	_
Nonwoven	12" x 12"	TX8932	_	TX8932S	_

Nonwoven



• 45% polyester / 55% cellulose nonwoven material with a cut edge, cleanroom manufactured, creating a durable wiper ideal for spill control, cleaning, and solution application.

STX 624 Sterile VersaWipe

- Manufactured to provide low levels of particles and extractables creating a wiper suitable for general cleaning and wiping.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Meets USP <797> and USP <800> wiper requirements.
- Autoclave safe.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
VersaWipe®	4" x 4"	TX624	_	STX624	_
	9" x 9"	TX629	_	_	_
	12" x 12"	TX622	_	_	_

INDUS	TRIES	
Aerospace	Animal Laboratory	
Biologics	Cleanroom Design/Build	
Cleanroom Environment	Compounding Pharmacies	
Data Storage	Facilities Maintenance	
Industrial	Laboratory	
Medical Device	Microelectronics	
Pharmaceutical	Printing/Graphics	
Semiconductor		



Specialty



	INDUSTRIES		
	Aerospace	Animal Laboratory	
	Biologics	Cleanroom Design/Build	
	Cleanroom Environment	Compounding Pharmacies	
	Data Storage	Facilities Maintenance	
	Industrial	Laboratory	
	Medical Device	Microelectronics	
	Pharmaceutical	Printing/Graphics	
	Semiconductor	USP <797> / USP <800>	

BetaWipe[®]

- Composite of polypropylene material and cellulose material with a cut edge and is cleanroom
 manufactured. Constructed by thermally bonding nonwoven polypropylene outer layers over
 cellulose inner layers creating a wiper ideal for spill control, cleaning, and solution application.
- Use on abrasive surfaces will not easily snag or abrade releasing particles and fibers into the process or environment.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Autoclave safe.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
BetaWipe®	9" x 9"	TX2009	_	_	_

Specialty



FoamWipe®

- Constructed from 100 ppi polyurethane foam material with a cut edge, and is cleanroom manufactured creating a high absorbency wiper ideal for spill control, cleaning, and solution application.
- Unique texture, ideal for picking up fine powder.
- Good chemical resistance for compatibility with a variety of solutions.
- Autoclave safe
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
FoamWipe®	6" x 6" x 1/8"	TX704	_	_	_

TRIES				
Animal Laboratory				
Cleanroom Design/Build				
Compounding Pharmacies				
Facilities Maintenance				
Laboratory				
Microelectronics				
Printing/Graphics				
USP <797> / USP <800>				

Specialty



INDUSTRIES				
Aerospace	Animal Laboratory			
Biologics	Cleanroom Design/Build			
Cleanroom Environment	Compounding Pharmacies			
Data Storage	Facilities Maintenance			
Industrial	Laboratory			
Medical Device	Microelectronics			
Pharmaceutical	Printing/Graphics			
Semiconductor	USP <797> / USP <800>			

TexWipe® and NuCotton®

- Constructed from long staple 100% cotton yarn with a cut edge, cleanroom manufactured to reduce free floating fibers on the surface while still providing excellent wiping and cleaning.
- Made from sustainable and renewable materials grown and processed in the United States.
- Use on abrasive surfaces will not easily snag or abrade releasing particles and fibers into the process or environment.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Autoclave safe.
- Bias-cut to minimize edge shedding and fraying.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
TexWipe®	4" x 4"	TX304	_	_	_
	6" x 6"	TX306	_	_	_
	9" x 9"	TX309	_	_	_
	12" x 12"	TX312	_	_	_
NuCotton®	9" x 9"	TX329	_	_	_

Specialty



NSF Rated



TX8723 PolySat® wipers are NSF rated to be acceptable for use as a general cleaner (A1) on all surfaces in and around food processing areas, where its use is not intended for direct food contact. Use of TX8723 in food processing or handling facilities requires that all food products and packaging materials be removed or protected prior to use of product. A potable water rinse of cleaned surfaces is required after use of this product. When used according to instructions, TX8723 PolySat® wipers will not exhibit a noticeable odor nor will it leave a visible residue.

PolySat[®]

- 100% melt-blown polypropylene with a cut edge, cleanroom manufactured, creating a soft wiper ideal for use on sensitive surfaces.
- Pre-wetted with 0.2 μm filtered 70% IPA / 30% DIW for ease of use and provide a consistent, optimized cleaning efficiency with repeatable wetness and VOC levels.
- Easy-to-use, reclosable slider bags, tubs, and peel-and-reseal bags reducing solution evaporation that preserves the consistent wiper wetness level.
- Manufactured to provide low levels of particles and extractables creating a wiper suitable for general cleaning and wiping.
- Use on abrasive surfaces will not easily snag or abrade releasing particles and fibers into the process or environment
- Meets USP <797> and <800> wiper requirements.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
PolySat®	6" x 11"	_	TX8723 TX8727	_	_
	7" x 11"	_	TX1040	_	_
	9" x 11"	_	TX1051	_	TX3213 TX3216

INDUSTRIES				
Aerospace	Animal Laboratory			
Biologics	Cleanroom Design/Buil			
Cleanroom Environment	Compounding Pharmacies			
Data Storage	Facilities Maintenance			
Food Processing	Industrial			
Laboratory	Medical Device			
Microelectronics	Pharmaceutical			
Printing/Graphics	Semiconductor			
USP <797>	/ USP <800>			

Specialty



	INDUSTRIES				
	Aerospace	Automotive			
	Cleanroom Environment	Printing/Graphics			
	Marine				

Cleanroom Wipers | texwipe.com

Mold Release® Sheets

- 100% durable, 2-ply spunbond polypropylene material with a cut edge, cleanroom manufactured, creating a low-linting chemical resistant wiper.
- Pre-wetted sheets provide consistent, accurate amounts of solvent for uniform application to mold surfaces.
- Point-of-use pouches designed for ease of use, minimizing exposure to hazardous vapors, lowering VOC emissions and eliminating potential for spills.
- Satin finish mold release.
- Quick cure at room temperature.
- Semi-permanent multiple releases.
- Optimized mold release usage.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
Mold Release® Sheets	7" x 11"	_	TX9406 TX9407	_	_

Specialty



- Pre-wetted wipers provide consistent, optimized cleaning efficiency with repeatable wetness and VOC levels.
- Canister delivery system is designed for ease of use at workstations, minimizing exposure to hazardous vapors, lowering VOC emissions and eliminating potential for spills.
- Easy-to-use solvent-resistant pouches that fit easily into a refillable canister designed to allow users to tear off wipers at the perforation for single wipe use.
- Individually lot coded for ease of traceability and quality control.

Collection	Size	Dry	Pre-Wetted	Dry Sterile	Pre-Wetted Sterile
SolvSat®	6" x 9"	_	TX8346 TX8347	_	_

- Meets Aerospace Standard BMS 15-5F, Class A.
- Meets Aerospace Standard DMS 1820E.
- Conforms to BMS 88-001 Class 4 nonwoven, 100% Rayon.

INDUSTRIES						
Aerospace	Automotive					
Cleanroom Environments	Marine					
Printing/Graphics						



Texwipe° I texwipe.com



Wipers / Mops / Swabs & Solutions Compatibility

				Disinfectants			Cleaners		
Material/ Fabric Polyester/	Texwipe Wiper Products	Texwipe Mop Products	Texwipe Swab Products	TexQ	TexTab™ TX6460	Texcide	Sea with rest. With re	TX 157 The state of the state o	Section 1
Cellulose	604, 606, 609, 612, 1109, 1112, 1118, 3210			^	•	•	V	•	
Microdenier (100% Polyester)	TX59, 3059	AlphaMops: TX7118M, STX7118M, TX7114M, STX7114M BetaMops:	Microdenier Series	1	√	√	√	√	✓
		TX7070, STX7070							
Polyester (100%)	TX1010, 1012, 1029, 1050, 1052, 1060, 1069, 1070, 1080, 8659, 1004, 1009, 1009B, 1013, 1008, 1008B, 2064, 2069, 2424, 2452, 2409, 2412, 2418, 49, 42, 29, 22	AlphaMops: TX7118, STX7118, TX7114, STX7114 BetaMops: TX716R, STX716R, TX7072, STX7072	Alpha Series, Absorbond Series Polyester Honeycomb Series		✓				
	TX3042, 3049, 3215, 3225, 3220, 3211, 3212, 3224, STX404, 409								
Polyester/ Rayon		BetaMops: TX7073, STX7073		X	✓	✓	✓	√	✓
Nylon	TX4004, TX4009, TX4012		TX730	X	✓	X	X	1	√
Cotton	TX304, TX306, TX309, TX312, TX329		Cotton Series	X	✓	✓	√	1	√
Foam	TX704		CleanFoam Series A, CleanFoam Series B, General Purpose Foam Series	✓	√	✓	✓	✓	✓
Polypropylene/ Cellulose	TX699, 2009			X	✓	✓	1	✓	✓

X =not compatible $\sqrt{} =$ compatible



Wiper Selection Guide

Collection /ERTEX® WI	Number	Size	Description	Packaging	Case	Page
VERTEX* WI	TX29	9" x 9" (23 cm x 23 cm)	Vertex® dry	150 wipers/bag (2 bags of 75)	10 bags	VERTEX®
	TX49	9" x 9" (23 cm x 23 cm)	Vertex® dry	75 wipers/bag (2 bags of 75)	10 bags	VERTEX®
	TX49P	9" x 9" (23 cm x 23 cm)	Vertex® pre-wetted; 70% IPA	75 wipers/reclosable bag	4 bags	VERTEX®
	TX3049	1 /			-	
Vertex®		9" x 9" (23 cm x 23 cm)	Vertex® dry, sterile	100 wipers/bag (5 bags of 20)	5 bags	VERTEX®
	TX3049P	9" x 9" (23 cm x 23 cm)	Vertex® pre-wetted; 70% IPA, sterile	25 wipers/reclosable bag	5 bags	VERTEX®
	TX3221	11" x 11" (28 cm x 28 cm)	Vertex® dry, sterile	100 wipers/bag (5 bags of 20)	5 bags	VERTEX®
	TX42	12" x 12" (30 cm x 30 cm)	Vertex® dry	100 wipers/bag	10 bags	VERTEX®
	TX42P	12" x 12" (30 cm x 30 cm)	Vertex® pre-wetted, 70% IPA	50 wipers/reclosable bag	4 bags	VERTEX®
	TX3042	12" x 12" (30 cm x 30 cm)	Vertex® dry, sterile	100 wipers/bag (5 packs of 20)	5 bags	VERTEX [®]
	TX3042P	12" x 12" (31 cm x 31 cm)	Vertex® pre-wetted, 70% IPA, sterile	25 wipers/reclosable bag	5 bags	VERTEX [®]
	TX3044P	12" x 12" (31 cm x 31 cm)	Vertex® pre-wetted, ethanol; 70% denatured ethanol, sterile	25 wipers/reclosable bag	5 bags	VERTEX®
ertov® Mioradoniar	TX59	9" x 9" (23 cm x 23 cm)	Vertex® microdenier	150 wipers/bag	10 bags	VERTEX ⁶
ertex® Microdenier	TX3059	9" x 9" (23 cm x 23 cm)	Vertex® microdenier, sterile	100 wipers/bag (5 packs of 20)	5 bags	VERTEX*
ECTRA® SE	ALED-E	ORDER WIPERS				
	TX1010	9" x 9" (23 cm x 23 cm)	Vectra® Alpha® 10, dry	100 wipers/bag (2 inner bags of 50)	10 bags	VECTRA
	TX8410	9" x 9" (23 cm x 23 cm)	AlphaSat® Vectra® Alpha® 10; pre-wetted; 100% IPA	50 wipers/reclosable bag	12 bags	VECTRA [©]
	TX8415	9" x 9" (23 cm x 23 cm)	AlphaSat® Vectra® Alpha® 10; pre-wetted; 6% IPA	50 wipers/reclosable bag	12 bags	VECTRA*
ctra®	TX3285	9" x 9" (23 cm x 23 cm)	AlphaSat® Vectra® Alpha® 10; pre-wetted; 70% IPA, sterile	20 wipers/flexpack	20 flexpacks	VECTRA
pha® 10	TX1012	12" x 12" (31 cm x 31 cm)	Vectra® Alpha® 10, dry	100 wipers/bag	10 bags	VECTRA
	TX3212	12" x 12" (31 cm x 31 cm)	Vectra® Alpha® 10, dry, sterile	100 wipers/bag (5 packs of 20)	5 bags	VECTRA
		1			-	
	TX3280	12" x 12" (31 cm x 31 cm)	AlphaSat® Vectra® Alpha® 10; pre-wetted; 70% IPA, sterile	50 wipers/flatpack	5 flatpacks	VECTRA
ctra® LT	TX8659	9" x 9" (23 cm x 23 cm)	Alpha® 10 Lo TiO2 dry	150 wipers/bag (2 inner bags of 75)	10 bags	VECTRA*
	TX8691	9" x 9" (23 cm x 23 cm)	QuanSat™ LT; QuanTex™ pre-wetted; 6% IPA	50 wipers/reclosable bag	12 bags	VECTRA
	TX1050	9" x 9" (23 cm x 23 cm)	Vectra® AlphaSorb® 10, dry	100 wipers/bag (2 inner bags of 50)	10 bags	VECTRA
ectra®	TX1057	9" x 9" (23 cm x 23 cm)	AlphaSat® Vectra® AlphaSorb® 10; pre-wetted, 10% IPA	40 wipers/reclosable bag	12 bags	VECTRA
phaSorb® 10	TX1052	12" x 12" (31 cm x 31 cm)	AlphaSorb® 10, dry	100 wipers/bag	6 bags	VECTRA
	TX3215	12" x 12" (31 cm x 31 cm)	AlphaSorb® 10, dry sterile	100 wipers/bag	5 bags	VECTRA
ctra® oneycomb® 10	TX1060	9" x 9" (23 cm x 23 cm)	Vectra® Honeycomb® 10, dry	100 wipers/bag (2 inner bags of 50)	10 bags	VECTRA
,	TX1080	9" x 9" (23 cm x 23 cm)	Vectra® QuanTex™	150 wipers/bag (2 inner bags of 75 wipers)	10 bags	VECTRA*
	TX1082	9" x 9" (23 cm x 23 cm)	Vectra® QuanSat™; pre-wetted; 100% IPA	50 wipers/reclosable bag	12 bags	VECTRA
ectra® QuanTex™	TX1084	9" x 9" (23 cm x 23 cm)	Vectra® QuanSat™; pre-wetted; 70% IPA	50 wipers/reclosable bag	12 bags	VECTRA
	TX1086	9" x 9" (23 cm x 23 cm)	Vectra® QuanSat™; pre-wetted; 6% IPA	50 wipers/reclosable bag	12 bags	VECTRA
ctra®	TX1029	9" x 9" (23 cm x 23 cm)	Vectra® Quantum®, dry	100 wipers/bag (2 inner bags of 50)	10 bags	VECTRA
uantum® 100	TX3224	· · · · · · · · · · · · · · · · · · ·	ToyTro® 10, dry storile		-	150701
-T® 10		9" x 9" (23 cm x 23 cm)	TexTra® 10; dry, sterile	100 wipers/bag (5 packs of 20)	6 bags	VECTRA*
xTra® 10	TX2452	12" x 12" (31 cm x 31 cm)	TexTra® 10; dry	100 wipers/bag	6 bags	VECTRA
T	TX3225	12" x 12" (31 cm x 31 cm)	TexTra® 10; dry, sterile	100 wipers/bag (2 inner bags of 20)	5 bags	VECTRA
xTube®	TX1070	9" x 9" (23 cm x 23 cm)	TexTube [®] , dry	100 wipers/bag (2 inner bags of 50)	10 bags	VECTRA
EALED-ED			T. W. L	000 1	00.1	
xVantage®	TX8944	4" x 4" (10 cm x 10 cm)	TexVantage® Polyester dry	300 wipers/bag (2 inner bags of 150)	20 bags	SEALED-ED
lyester	TX8949	9" x 9" (23 cm x 23 cm)	TexVantage® Polyester dry	150 wipers/bag (2 inner bags of 75)	10 bags	SEALED-ED
	TX8942	12" x 12" (30 cm x 30 cm)	TexVantage® Polyester dry, sterile	100 wipers/bag	10 bags	SEALED-ED
ermaSeal® 60	TX2064	4" x 4" (10 cm x 10 cm)	ThermaSeal® 60; dry	300 wipers/bag (2 inner bags of 150)	20 bags	SEALED-ED
omaooa 00	TX2069	9" x 9" (23 cm x 23 cm)	ThermaSeal® 60; dry	150 wipers/bag (2 inner bags of 75)	10 bags	SEALED-ED
	TX1204	4" x 4" (10 cm x 10 cm)	Alpha® 1 Microfiber; dry	100 wipers/bag (2 bags of 50 wipers)	20 bags	SEALED-ED
	TX1206	6" x 6" (15 cm x 15 cm)	Alpha® 1 Microfiber; dry	100 wipers/bag (2 bags of 50 wipers)	20 bags	SEALED-ED
oha® 1	TX1209	9" x 9" (23 cm x 23 cm)	Alpha® 1 Microfiber; dry	100 wipers/bag (2 bags of 50 wipers)	20 bags	SEALED-ED
icrofiber	STX1209	9" x 9" (23 cm x 23 cm)	Alpha® 1 Microfiber; dry, sterile	100 wipers/bag (4 bags of 25 wipers)	5 bags	SEALED-ED
	TX1212	12" x 12" (31 cm x 31 cm)	Alpha® 1 Microfiber; dry	100 wipers/bag (2 bags of 50 wipers)	10 bags	SEALED-ED
	STX1212	12" x 12" (31 cm x 31 cm)	Alpha® 1 Microfiber; dry, sterile	100 wipers/bag (4 bags of 25 wipers)	5 bags	SEALED-EI
UT-EDGE V			i i i i i i i i i i i i i i i i i i i	,	J Sugo	22 320 11
	TX1008	9" x 9" (23 cm x 23 cm)	AlphaLite® dry	150 wipers/bag (2 inner bags of 75)	10 bags	CUT-EDG
ohaLite®	TX1008B	9" x 9" (23 cm x 23 cm)	AlphaLite® dry, bulk packed	150 wipers/bag (2 inner bags of 75)	10 bags	CUT-EDG
	TX2409	9" x 9" (23 cm x 23 cm)	AlphaSorb® HC, dry	100 wipers/bag (2 inner bags of 50)	10 bags	CUT-EDG
	TX2412	12" x 12" (31 cm x 31 cm)	AlphaSorb® HC; dry	100 wipers/bag (2 inner bags of 50)	6 bags	CUT-EDG
ohaSorb® HC	TX3252	12" x 12" (31 cm x 31 cm)		25 wipers/flatpack	5 flatpacks	CUT-EDG
		1 /	AlphaSorb® HC; pre-wetted, 70% IPA, sterile	<u> </u>		
	TX2418	18" x 18" (46 cm x 46 cm)	AlphaNina® dn/	100 wipers/bag (2 inner bags of 50)	3 bags	CUT-EDG
AlphaWipe®	TX1004	4" x 4" (10 cm x 10 cm)	AlphaWipe®, dry	300 wipers/bag (2 inner bags of 150)	20 bags	CUT-EDG
	TX1034	4" x 4" (10 cm x 10 cm)	AlphaSat® AlphaWipe® pre-wetted, 70% IPA	200 wipers/reclosable bag	4 bags	CUT-EDG
	STX1004	4" x 4" (10 cm x 10 cm)	AlphaWipe® dry, sterile	50 wipers/bag	50 bags	CUT-EDG
	STX1034	4" x 4" (10 cm x 10 cm)	AlphaSat® AlphaWipe® pre-wetted, 70% IPA, sterile	50 wipers/reclosable bag	8 bags	CUT-EDG
	TX1036	6" x 6" (15 cm x 15 cm)	AlphaSat® AlphaWipe® pre-wetted, 70% IPA	75 wipers/reclosable bag	12 bags	CUT-EDG
	TX1009	9" x 9" (23 cm x 23 cm)	AlphaWipe® dry	150 wipers/bag (2 inner bags of 150 wipers)	10 bags	CUT-EDG
	TX1009B	9" x 9" (23 cm x 23 cm)	AlphaWipe® dry, bulk packed	150 wipers/bag (2 inner bags of 150 wipers)	10 bags	CUT-EDG
	TX1039	9" x 9" (23 cm x 23 cm)	AlphaSat® AlphaWipe® pre-wetted, 70% IPA	50 wipers/reclosable bag	4 bags	CUT-EDG



Theor Co	10000	or Grandia				
Collection	Number	Size	Description	Packaging	Case	Page
	TX7031	9" x 31" (23 cm x 79 cm)	AlphaSat® AlphaWipe® pre-wetted, 6% IPA	25 wipers/reclosable bag	4 bags	CUT-EDGE 4
AlphaWipe®	TX1031	9" x 32" (23 cm x 81 cm)	AlphaWipe®; dry	20 wipers/bag	10 bags	CUT-EDGE 4
(continued)	TX1013	12" x 12" (31 cm x 31 cm)	AlphaWipe® dry	75 wipers/bag; double bagged	10 bags	CUT-EDGE 4
	TX1025	24" x 44" (60 cm x 111 cm)	AlphaWipe® dry	25 wipers/bag	3 bags	CUT-EDGE 4
	TX4004	4" x 4" (10 cm x 10 cm)	MiracleWipe® dry	600 wipers/bag (4 inner bags of 150)	8 bags	CUT-EDGE 5
MiracleWipe®	TX4009	9" x 9" (23 cm x 23 cm)	MiracleWipe® dry	150 wipers/bag (3 inner bags of 50)	8 bags	CUT-EDGE 5
	TX4012	10" x 12" (25 cm x 31 cm)	MiracleWipe® dry	200 wipers/bag (4 inner bags of 50)	4 bags	CUT-EDGE 5
TovTro®	TX2424	12" x 12" (31 cm x 31 cm)	TexTra® dry	100 wipers/bag (2 inner bags of 50)	6 bags	CUT-EDGE 5
TexTra [®]	TX3220	12" x 12" (31 cm x 31 cm)	,		5 bags	
NONWOVEN			TexTra®; dry, sterile	100 wipers/bag (5 inner bags of 20)	Suays	CUT-EDGE 5
NONWOVEN			Alexandra and Control	1 000 in any financ (4 in any harra of 200)	10 hans	
Absorbond®	TX404	4" x 4" (10 cm x 10 cm)	Absorbond®; dry	1,200 wipers/bag (4 inner bags of 300)	10 bags	NONWOVEN 2
	TX409	9" x 9" (23 cm x 23 cm)	Absorbond®; dry	300 wipers/bag (2 inner bags of 150)	10 bags	NONWOVEN 2
BlueWipe®	TX512	12" x 12" (31 cm x 31 cm)	BlueWipe® dry	50 wipers/bag	10 bags	NONWOVEN 3
ProCell®	TX699	9" x 9" (23 cm x 23 cm)	ProCell [™] dry	150 wipers/bag	12 bags	NONWOVEN 4
	TX604	4" x 4" (10 cm x 10 cm)	TechniCloth® dry	1,200 wipers/bag (4 packs of 300)	10 bags	NONWOVEN 5
	TX606	6" x 6" (15 cm x 15 cm)	TechniCloth® dry	600 wipers/bag (2 packs of 300)	10 bags	NONWOVEN 5
	TX609	9" x 9" (23 cm x 23 cm)	TechniCloth® dry	300 wipers/bag	10 bags	NONWOVEN 5
		9" x 9" (23 cm x 23 cm)			-	
	STX609		TechniCloth® dry, sterile	100 wipers/bag (4 packs of 25)	5 bags	NONWOVEN 5
	TX612	12" x 12" (31 cm x 31 cm)	TechniCloth® dry	150 wipers/bag	10 bags	NONWOVEN 5
	TX3210	12" x 12" (31 cm x 31 cm)	TechniCloth® dry, sterile	100 wipers/bag (5 packs of 20)	5 bags	NONWOVEN 5
	TX1045	6" x 8" (15 cm x 20 cm)	TechniSat® TechniCloth® pre-wetted, 70% IPA	100 wipers/canister	12 canisters	NONWOVEN 5
	TX1067	7" x 11" (18 cm x 28 cm)	TechniSat® TechniCloth® pre-wetted, 70% IPA	200 wipers/reclosable bag	4 bags	NONWOVEN 5
TechniCloth®	TX1068	7" x 11" (18 cm x 28 cm)	TechniSat® TechniCloth® pre-wetted, 70% ethanol	50 wipers/flexpack	20 flexpacks	NONWOVEN 5
TOOTH HOIOUT	STX1068	7" x 11" (18 cm x 28 cm)	TechniSat® TechniCloth® pre-wetted, 70% ethanol, sterile	50 wipers/flexpack	20 flexpacks	NONWOVEN 5
	TX1048	8" x 5" (20 cm x 13 cm)	TechniSat® TechniCloth® pre-wetted, 6% IPA	210 wipers/refill pack	12 refill packs	NONWOVEN 5
		,	' '	' '	& 1 tub	
	STX1041	8" x 5.5" (20 cm x 14 cm)	TechniSat® TechniCloth® pre-wetted, 70% IPA, sterile	50 wipers/reclosable bag	8 bags	NONWOVEN 5
	TX1041	9" x 11" (23 cm x 28 cm)	TechniSat® TechniCloth® pre-wetted, 70% IPA	70 wipers/reclosable bag	12 bags	NONWOVEN 5
	TX1065	9" x 11" (23 cm x 28 cm)	TechniSat® TechniCloth® pre-wetted, 70% IPA	50 wipers/flexpack	20 flexpacks	NONWOVEN 5
	TX3214	9" x 11" (23 cm x 28 cm)	TechniSat® TechniCloth® pre-wetted, 70% IPA, sterile	50 wipers/flexpack	20 flexpacks	NONWOVEN 5
	TX3217	9" x 11" (23 cm x 28 cm)	TechniSat® TechniCloth® pre-wetted, 70% IPA, sterile	20 wipers/flexpack	24 flexpacks	NONWOVEN 5
	TX8488	9" x 11" (23 cm x 28 cm)	TechniSat® TechniCloth® pre-wetted, 6% IPA	300 wipers/resealable bag	3 bags	NONWOVEN 5
	TX1109	9" x 9" (23 cm x 23 cm)	TechniCloth® II dry	300 wipers/bag	10 bags	NONWOVEN 6
TechniCloth® II	TX1112	12" x 12" (31 cm x 31 cm)	TechniCloth® II dry	150 wipers/bag	10 bags	NONWOVEN 6
	TX1118	18"x 18" (46 cm x 46 cm)	TechniCloth® II dry	75 wipers/bag	10 bags	NONWOVEN 6
	TX4409	9" x 9" (23 cm x 23 cm)	TechniScrub™ dry	100 wipers/bag	10 bags	NONWOVEN 7
TechniScrub™	TX4412	12" x 12" (31 cm x 31 cm)	TechniScrub™ dry	100 wipers/bag	10 bags	NONWOVEN 7
	TX8939	9" x 9" (23 cm x 23 cm)	TexVantage® Nonwoven dry	300 wipers/bag (2 inner bags of 150)	20 bags	NONWOVEN 8
TexVantage®	TX8932	12" x 12" (31 cm x 31 cm)	TexVantage® Nonwoven dry	150 wipers/bag (2 inner bags of 75)	10 bags	NONWOVEN 8
Nonwoven	TX8932S	12" x 12" (31 cm x 31 cm)	TexVantage® Nonwoven dry, sterile	100 wipers/bag	10 bags	NONWOVEN 8
					-	
	TX624	4" x 4" (10 cm x 10 cm)	VersaWipe® dry	1,200 wipers/bag (2 inner bags of 600)	10 bags	NONWOVEN 9
VersaWipe®	STX624	4" x 4" (10 cm x 10 cm)	VersaWipe® dry, sterile	50 wipers/bag	50 bags	NONWOVEN 9
•	TX629	9" x 9" (23 cm x 23 cm)	VersaWipe® dry	300 wipers/bag	10 bags	NONWOVEN 9
			VersaWipe® dry	150 wipers/bag	10 bags	NONWOVEN 9
SPECIALTY	WIPERS	S				
BetaWipe®	TX2009	9" x 9" (23 cm x 23 cm)	BetaWipe® dry	100 wipers/bag (2 inner bags of 50)	10 bags	SPECIALTY 2
FoamWipe®	TX704	6" x 9" x 1/8" (15 cm x 23 cm x 3 mm)	FoamWipe® dry	60 wipers/bag	8 bags	SPECIALTY 3
•		,	' '	· · ·	-	
	TX304	4" x 4" (10 cm x 10 cm)	TexWipe® dry	1,200 wipers/bag (4 inner bags of 300)	6 bags	SPECIALTY 4
TexWipe® and	TX306	6" x 6" (15 cm x 15 cm)	TexWipe® dry	600 wipers/bag (2 inner bags of 300)	6 bags	SPECIALTY 4
NuCotton®	TX309	9" x 9" (23 cm x 23 cm)	TexWipe® dry	300 wipers/bag (2 inner bags of 150)	6 bags	SPECIALTY 4
	TX329	9" x 9" (23 cm x 23 cm)	NuCotton® dry	300 wipers/bag	6 bags	SPECIALTY 4
	TX312	12" x 12" (31 cm x 31 cm)	TexWipe® dry	150 wipers/bag	6 bags	SPECIALTY 4
	TX1040	7" x 11" (17 cm x 28 cm)	PolySat® pre-wetted, 70% IPA	200 wipers/reclosable bag	4 bags	SPECIALTY 5
	TX1051	9" x 11" (23 cm x 28 cm)	PolySat® pre-wetted, 70% IPA	50 wipers/flexpack	24 flexpacks	SPECIALTY 5
	TX3213	9" x 11" (23 cm x 28 cm)	PolySat® pre-wetted, 70% IPA, sterile	50 wipers/flexpack	20 flexpacks	SPECIALTY 5
PolySat®	TX3216	9" x 11" (23 cm x 28 cm)	PolySat® pre-wetted, 70% IPA, sterile	20 wipers/flexpack	24 flexpacks	SPECIALTY 5
,	TX8723	6" x 11" (15 cm x 28 cm)	PolySat® pre-wetted, 70% IPA	75 wipers/bag	24 bags	SPECIALTY 5
	TX8727	6" x 11" (15 cm x 28 cm)	PolySat® pre-wetted, 70% IPA refills	75 wipers/refill bag	20 bags, reclosable	SPECIALTY 5
	TV0400	7" v 11" /17 om v 00 om\	Pro watted 05 ml 100% Frakets 55 NO	5 chaote/pouch	container	ODEOMIE C
Mold Release Sheets	TX9406	7" x 11" (17 cm x 28 cm)	Pre-wetted, 95 ml 100% Frekote 55-NC	5 sheets/pouch	20 pouches	SPECIALTY 6
	TX9407 TX8346	7" x 11" (17 cm x 28 cm) 6" x 9" (15 cm x 23 cm)	Pre-wetted, 190 ml 100% Frekote 55-NC SolvSat®; pre-wetted, 99.5% acetone	10 sheets/pouch 100 wipers/pouch	20 pouches 10 pouches 2 pre-labeled	SPECIALTY 6 SPECIALTY 7
SolvSat® -		,			containers 10 pouches	
	TX8347	6" x 9" (15 cm x 23 cm)	SolvSat®; pre-wetted, 99.9% IPA	100 wipers/pouch	2 pre-labeled containers	SPECIALTY 7





 Americas
 +1 336 996 7046

 EMEA
 +31 88 1307 410

 Philippines
 +63 49 543 0241

 China
 +86 512 6303 3700

www.texwipe.com